

Technical Data Sheet: Water Softeners

SL150 NON-ELECTRIC WATER SOFTENER - STANDARD

EAN	5027639900100
Product Code	900100
People	Up to 5
Height	470mm
Depth	483mm
Depth (With Connectors)	543mm
Width	240mm
Flow Rate @ 1 bar Pressure Drop	25 L/Minute
Approximate Regeneration Time	15 Minutes
Resin Volume	3.3 Litre (Ultra Fine)
Salt used per regeneration	0.33kg
Water used per regeneration	18 Litre
Inlet & Outlet	3/4" BSP
Drain & Overflow	1/2"
Includes	2 x Standard 15mm Hoses
Hi-Flo Option	Code 900131
Power Source	None (Water Pressure)
Installation Orientation	Left / Right / Rear
Minimum / Maximum Ambient Temp	2°- 40°C
Minimum / Maximum Working Pressure	1 bar min / 6 bar max*
* Pressure reducing valve must be used over 6 bar	
Maximum Soft Water (at 200 ppm)	750 Litres
Maximum Soft Water (at 300 ppm)	500 Litres
What salt to use	Tablet or Block
Warranty	2 Years Parts and Labour*



* IMPORTANT: To qualify for warranty the softener must be registered and installed in accordance with the Manufacturers installation instructions. Warranty does not cover incorrect installation or setting up of the softener, site damage or resin contamination.

TECHNICAL HELPLINE 01785 811636



Technical Data Sheet: Water Softeners

SL150 NON-ELECTRIC WATER SOFTENER - HIGH FLOW

EAN	5027639900131
Product Code	900131
People	Up to 5
Height	470mm
Depth	483mm
Depth (With Connectors)	543mm
Width	240mm
Flow Rate @ 1 bar Pressure Drop	33 L/Minute
Approximate Regeneration Time	15 Minutes
Resin Volume	3.3 Litre (Ultra Fine)
Salt used per regeneration	0.33kg
Water used per regeneration	18 Litre
Inlet & Outlet	3/4" BSP
Drain & Overflow	1/2"
Includes	2 x Hi-Flow 22mm Hoses
Power Source	None (Water Pressure)
Installation Orientation	Left / Right / Rear
Minimum / Maximum Ambient Temp	2°- 40°C
Minimum / Maximum Working Pressure	1 bar min / 6 bar max*
* Pressure Reducing Valve Must Be Used Over 6 bar	
Maximum Soft Water (at 200 ppm)	750 Litres
Maximum Soft Water (at 300 ppm)	500 Litres
What salt to use	Tablet or Block
Warranty	2 Years Parts and Labour*



* IMPORTANT: To qualify for warranty the softener must be registered and installed in accordance with the Manufacturers installation instructions. Warranty does not cover incorrect installation or setting up of the softener, site damage or resin contamination.

TECHNICAL HELPLINE 01785 811636